

Automatic burettes, Pellet pattern, without intermediate stopcock, Schellbach, BLAUBRAND® Brand



Borosilicate glass 3.3, class AS, conformity certified

- Calibrated to deliver 'TD, Ex'
- Schellbach stripe, ring marks at major graduations
- Automatic zeroing, needle-valve stopcock with PTFE spindle, without intermediate stopcock

DIN EN ISO 385

Ordering information: Supplied with a batch certificate. Burettes are also available on request with an individual certificate, a USP individual certificate or a DAkkS calibration certificate.

Capacity (ml)	Division (ml)	Tolerance (± ml)	Total height (mm)	Pk	Cat. No.
Automatic burette supplied with 2 litre reservoir bottle (soda-lime glass)					
10	0,02	0,02	1000*	1	661-2114
25	0,05	0,03	1000*	1	612-2864
50	0,1	0,05	1000*	1	612-2865

*Total height includes the reservoir bottle

Burettes, Pellet pattern, without intermediate stopcock, Schellbach Hirschmann Laborgeräte



DURAN®, borosilicate glass, class AS

- Calibrated to deliver 'Ex', conformity certified with dated batch identification
- Schellbach stripe, ring marks at major graduations, blue graduations
- Automatic zeroing, PTFE spindle and without intermediate stopcock

DIN EN ISO 385

Delivery information: Supplied with 2 litre glass reservoir bottle.

Capacity (ml)	Division (ml)	Tolerance (± ml)	Pk	Cat. No.
10	0,02	0,02	1	612-9927
25	0,05	0,03	1	612-9928
50	0,1	0,05	1	612-9929

Automatic burettes, Pellet pattern, with intermediate stopcock, Schellbach, BLAUBRAND® Brand



Borosilicate glass 3.3, class AS, conformity certified

- Calibrated to deliver 'TD, Ex'
- Schellbach stripe, ring marks at major graduations
- Automatic zeroing, intermediate stopcock to recirculate residual liquid

DIN EN ISO 385

Ordering information: Burettes are also available on request with an individual certificate, a USP individual certificate or a DAkkS calibration certificate.

Delivery information: Supplied with 2 litre (soda-lime glass) reservoir bottle and batch certificate.

Capacity (ml)	Division (ml)	Tolerance (± ml)	Total height (mm)	Pk	Cat. No.
Needle-valve stopcock (PTFE key in intermediate stopcock)					
10	0,02	0,02	~1000	1	612-9910
25	0,05	0,03	~1000	1	612-9911
50	0,10	0,05	~1000	1	612-9912
Glass stopcock (glass key in intermediate stopcock)					
10	0,02	0,02	~1000	1	612-9913
25	0,05	0,03	~1000	1	612-9914
50	0,10	0,05	~1000	1	612-9915