



## Adapters, reduction, for standard ground joints



Quickfit®, borosilicate glass, clear

Reduction adapter from large cone at the base to small socket on the top.

- Very good chemical resistance
- High temperature resistance
- Minimal thermal expansion giving relatively high resistance to temperature changes

Cone size (NS)	Socket size (NS)	Pk	Cat. No.
14/23	10/19	2	201-0639
19/26	14/23	2	201-2357
24/29	14/23	2	201-0255
29/32	14/23	2	201-8344
24/29	19/26	2	201-0111
29/32	19/26	2	201-8346
34/35	19/26	2	201-0112
29/32	24/29	2	201-8349
34/35	24/29	2	201-2375
40/38	24/29	1	201-0131
45/40	24/29	1	201-0132
50/42	24/29	1	201-0640
55/44	24/29	1	201-0147
34/35	29/32	2	201-0150
45/40	29/32	1	201-0641
40/38	34/35	1	201-0642
45/40	34/35	1	201-0643
50/42	34/35	1	201-0644



## Adapters, expansion, for standard ground joints



PYREX®, borosilicate glass, Quickfit® joints, clear

Expansion adapter from large socket on the top to small cone at the base.

- Very good chemical resistance
- High temperature resistance
- Minimal thermal expansion giving relatively high resistance to temperature changes

Cone size (NS)	Socket size (NS)	Pk	Cat. No.
10/19	14/23	2	201-0704
14/23	19/26	2	201-0229
14/23	24/29	2	201-0230
19/26	24/29	2	201-0235
14/23	29/32	2	201-0236
19/26	29/32	2	201-0237
24/29	29/32	2	201-0238
19/26	34/35	2	201-0705
24/29	34/35	2	201-0706
29/32	34/35	2	201-0707
29/32	40/38	1	201-8767
29/32	45/40	1	201-0708
34/35	50/42	1	201-0709



**VWR CATALYST**  
We Enable Science Through Services

## VWR CATALYST SERVICES

Delivering complete solutions in and around the  
laboratory and production area

Please visit us at: [vwr.com/vwrcatalyst](http://vwr.com/vwrcatalyst)