



Beakers, low form



PP, highly translucent

Ideal for general laboratory use. With spout and easy to read blue graduations.

- Good chemical resistance
- Resistant to heat up to +121 °C (for 20 minutes), prolonged use at +100 °C
- Smooth surfaces for easy, fast cleaning

ISO 7056

| Capacity (ml) | Height (mm) | Ø ext. (mm) | Division (ml) | Pk | Cat. No. |
|---------------|-------------|-------------|---------------|----|----------|
| 25            | 50          | 38          | 5             | 12 | 213-1621 |
| 50            | 60          | 47          | 10            | 12 | 213-1622 |
| 100           | 70          | 55          | 10            | 12 | 213-1623 |
| 250           | 95          | 77          | 25            | 6  | 213-1624 |
| 400           | 111,5       | 87          | 50            | 1  | 213-1725 |
| 600           | 126,5       | 100         | 50            | 1  | 213-1726 |
| 1000          | 147         | 120         | 100           | 1  | 213-1642 |
| 2000          | 187         | 149         | 200           | 1  | 216-1643 |
| 3000          | 212         | 170         | 250           | 1  | 219-1644 |
| 5000          | 247         | 203         | 500           | 1  | 222-1645 |

Beakers, low form  
Brand



PP, high clarity

With printed blue scale, beaded rim and spout.

- Very good chemical resistance
- Cleaning up to max. +60 °C is recommended to preserve marks and inscriptions
- For autoclaving (+121 °C) beakers with an embossed scale should be selected

ISO 7056

| Capacity (ml) | Height (mm) | Ø ext. (mm) | Division (ml) | Pk | Cat. No. |
|---------------|-------------|-------------|---------------|----|----------|
| 10*           | 36          | 30          | 2             | 12 | 213-0377 |
| 25            | 50          | 38          | 5             | 12 | 213-0378 |
| 50            | 60          | 47          | 10            | 12 | 213-0379 |
| 100           | 70          | 55          | 10            | 12 | 213-0380 |
| 150*          | 80          | 66          | 20            | 12 | 213-0381 |
| 250           | 95          | 77          | 25            | 6  | 213-0382 |
| 400*          | 112         | 87          | 50            | 6  | 213-0383 |
| 500           | 118         | 94          | 50            | 6  | 213-0384 |
| 600*          | 127         | 100         | 50            | 6  | 213-0385 |
| 1000          | 147         | 120         | 100           | 6  | 213-0386 |
| 2000          | 187         | 149         | 200           | 6  | 213-0387 |
| 3000*         | 212         | 170         | 250           | 4  | 213-0388 |
| 5000          | 247         | 203         | 500           | 4  | 213-0389 |

\* In addition to ISO 7056



VWR COLLECTION

Delivering high quality and superior performance

Please contact your local VWR sales office or go to [vwr.com](http://vwr.com) for the latest news and special offers